



APD72-D

APD72-D Automatic Dehydrator, 0.58 SCFM, 230V AC 50/60 Hz

The APD-D series Automatic Pressurization Dehydrator is designed for reliable pressurization of elliptical waveguide, coaxial cable and rigid transmission line systems. Dry pressurized air in the distribution system ensures that condensation is avoided and optimal system performance is achieved.

The dehydrator includes a self-contained completely automated air drying system that utilizes a pressure swing moisture adsorption cycle to provide pressurized dry air while continuously purging the collected moisture to the atmosphere. This eliminates the need for replacement or manual reactivation of the desiccant and makes our APD-D series dehydrators ideal for unattended operation, even at remote sites.

The dehydration system is completely automatic, with no need for periodic media replacement or reactivation. These units are capable of years of trouble-free service when properly installed, operated and maintained.

An internal check valve guarantees that the customer system stays isolated from the dehydrator's internal system when the dehydrator is not actively operating. A USB port offers the ability to enable options, update configurations and download operating data in the field for easy upgrade, maintenance and troubleshooting.

The alarm port consists of electrically isolated 1 Form C relay contacts that can be used for both local and/or remote monitoring/alarming. Additional standard features include a 0-103 kPa (0-15 psig) pressure gauge and indicating LED lights.

The units may be shelf mounted or placed in a 19" EIA relay rack. A Wall/Rack mount is available as an optional accessory.

FEATURES / BENEFITS

- Low Pressure Operation - Software configurable from 6.7-17.2 kPa (1-2.5 psig) in 3.4 kPa (0.5 psig) increments
- High Pressure Alarm - Software configurable from 20.7-75.8 kPa (3-11 psig) in 6.9 kPa (1 psig) increments
- Humidity Alarm - Software configurable from 20-50% RH in 10% RH increments
- Run Time Alarm - Software configurable from 10 minutes to 4 hours in 10 minute increments
- System Purge - Software configurable from 2-10 days in 2 day increments



Dehydrator

Technical features

GENERAL SPECIFICATIONS

Dehydrator Type		Automatic
System Capacity		High
60 Hz Output Capacity NI/h (SCFM)		1190 (0.7)
50 Hz Output Capacity NI/h (SCFM)		990 (0.58)
Output Dew Point	°C (°F)	Ambient dew point greater than 10°C (50°F): 50 (90) dew point reduction minimum. Ambient dew point less than 10°C (50°F): -40 (-40) dew point minimum
Field Adjustable Output Pressure (on/off)	kPa (psig)	Software configurable from 6.9 -68.9 (1-10)
Field Adjustable Output Pressure Deadband (on/off)	kPa (psig)	Software configurable from 13.8-62.1 (2-9)
High Pressure Safety Relief Valve	kPa (psig)	103.4 (15) fixed
Number of Outlets		1
Output Fitting		Quick-Connect 3/8" OD Plastic Tube (Note 3)
Max System Volume	l (ft³)	13500 (477)
Maximum Continuous Operation Time, Active	Hours	4



APD72-D

APD72-D Automatic Dehydrator, 0.58 SCFM, 230V AC 50/60 Hz

ELECTRICAL SPECIFICATIONS

Operating Voltage	V	230 +/- 10%
Frequency	Hz	47 - 63
Max. Standy Current	A	0.5
Max. Active Current	A	4
Max. Apparent Power Consumption	VA	440
Power Factor Correction	typical	0.8
Electrical Feed Circuit Configuration		Single phase, 3-Conductor (Phase/Neutral/Ground) (Note 4)
Electrical Feed Circuit Size Recommendation	A	15 (Note 5)
Electrical Inlet Connector		IEC 320 Type C 14

ENVIRONMENTAL

Ambient Temperature Range	°C (°F)	0 to 40 (32 to 104)
Ambient Humidity Range, relative	%	5-85, non-condensing (max absolute humidity 25g/m ³ (0.00156lb/ft ³)) (Note 2)
Noise, dBA @ 1 m, Active	dBA	66
Max.Operational Altitude @ 34.5 kPa (5 psig)	m (ft)	2900 (9500)
Max. Operational Altitude @ 68.9 kPa (10 psig)	m (ft)	2380 (7800)
Capacity derating per 305 m (1000 ft) altitude above MSL	l/h (CFM)	102 (0.06)

ACCESSORIES

Accessory/Spare Part		Wall/rack mount
----------------------	--	-----------------

ALARMS

Low Pressure Alarm		Standard configuration: Fixed at 3.4 kPa (0.5 psi) below lower operational pressure Low Pressure configuration: Fixed at 1.7 kPa (0.25 psig)
Alarm Contact Rating		1A, 30 VDC, maximum
Alarm Configuration		1 Form C relay contacts, screw terminal connector

OPTIONS

Options		<ul style="list-style-type: none"> Low Pressure Operation: Software configurable from 6.9 - 17.2 kPa (1-2.5 psig) in 3.4 kPa (0.5 psig) increments (Note 6) High Pressure Alarm: Software configurable from 20.7- 75.9 kPa (3-11 psig) in 6.9 kPa (1 psig) increments Humidity Alarm: Software configurable from 20-50% RH in 10% RH increments Run Time Alarm: Software configurable from 10 minutes to 4 hours in 10 minute increments System Purge: Software configureable from 2-10 days in 2 days increments
---------	--	--

COMPLIANCE

Compliance		<ul style="list-style-type: none"> CE (EMC, MD, PED, RoHS) IEC 60529, IP20
------------	--	--

External Document Links

Dehydrator

User's Guide, #60240001150, Rev. E, which includes:

- Installation instructions (p. 5)
- Troubleshooting (p. 6)

- Operation (p. 8)
- Alarm pin-out diagram (p. 15)
- Parts List (p. 18)
- Run Time Calculator (p. 22)
- Transmission Volume Calculator (p. 23)

REV : C

REV DATE : 29 Sep 2021

www.rfsworld.com



APD72-D

APD72-D Automatic Dehydrator, 0.58 SCFM, 230V AC 50/60 Hz

Notes

- 1) All specifications at 23°C (73°F) and 50% relative humidity at mean sea level (MSL) unless otherwise noted.
- 2) For indoor use only. IEC 60721-3-3 Class 3k3 (temperature-controlled locations, humidity not controlled)
absolute Humidity AH 25 g/m³ (0.00156 lb/ft³) @ 29.4°C (85°F) => 85 % relative humidity RH
absolute Humidity AH 25 g/m³ (0.00156 lb/ft³) @ 40°C (104°F) => 48.8 % relative humidity RH
- 3) Tubing used must be polyurethane (durometer 95A), polyethylene (durometer 440), or nylon (durometer 500)
- 4) Voltage source per IEC 60038 (1/N/PE)
***** Not for use with North American 240VAC service *****
- 5) Electrical supply circuit must retain within operating voltage specifications at all times.
- 6) Lower Operating Pressure set to 3.4 kPa (0.5 psig). Low Pressure alarm set to 1.7 kPa (0.25 psig)
- 7) The power cord is not included because the standard depends on the country where the dehydrator will be installed. It has to be purchased separately.